

FP 150 DIAPHRAGM LIQUID PUMP





ADVANTAGES

- Low pulsation
- Excellent linearity
- Self-priming and can run dry
- Gentle conveying of sensitive media
- Long lifetime,
 no maintenance
- Able to transfer aggressive media
- IP 65



Please visit our website www.knf.com to get more information.

POSSIBLE AREAS OF USE

- Inkiet printing
- Medical technology
- Laboratory technology
- Fuel cells
- Semiconductor industry
- And many more


PERFORMANCE DATA				
Series model	FP 150	FP 150		
Material options	KP	КТ		
Pump head	PP	PP		
Diaphragm	PTFE coated	PTFE coated		
Valves / O-rings	EPDM	FFKM / FKM		
Flow rate (I/min)	1.5	1.3		
Suction height (mH ₂ O)	2.7	2.5		
Pressure head (mH ₂ O)	20	20		
Permissible media temperature (°C)	5 - 80	5 - 80		
Permissible ambient temperature (°C)	5 - 40	5 - 40		
Protection factor	IP 65	IP 65		
Weight (kg)	0.8	0.8		
ELECTRICAL DATA				
Voltage (V)	24	24		
Motor	DCB-4	DCB-4		
Power (W) start at 5°C ambient	31	31		
I (A) start at 5°C ambient	1.3	1.3		
I (A) start at 25°C ambient	1.1	1.1		
Wires	AWG22	AWG22		
Input signal	Vctrl / PWM inverse	Vctrl / PWM inverse		
Input signal range Vctrl	05 V	05 V		
Input signal range PWM inverse	100%0%	100%0%		
VARIOUS				
Dimensions LxWxH (mm)	139x94x77	139x94x77		
Hydraulic connections	G 1/8"	G 1/8"		
Hose diameter recommendation (mm)	ID 8	ID 8		


FP 150 KPDCB-4


PERFORMANCE DATA				
Series model	Flow rate at atm. pressure (I/min)	Max. suction height (mH2O)	Max. pressure head (mH2O)	
FP 150 KPDCB-4	1.5	2.7	20	


FP 150 KTDCB-4


PERFORMANCE DATA				
Series model	Flow rate at atm. pressure (I/min)	Max. suction height (mH ₂ O)	Max. pressure head (mH ₂ O)	
FP 150 KTDCB-4	1.3	2.5	20	














ACCESSORIES					
Description	Illustration	Details			
Pulsation damper		This versatile pulsation damper reduces hydraulic pressure pulsations and vibrations in hoses and pipes. It helps to remove pulsation which prevents the system from functioning correctly. It also protects instrumentation connected after the pump.			
Mounting plate		Enabling additional mounting options. Screws included in the set.			
Mounting clamp		Additional fixing possibility by means of a pipe clamp on the pump.			

The performance values for the series models shown on this data sheet were determined under test conditions. The actual performance values may differ and depend in particular on the usage conditions and therefore on the specific application, on the parameters of the components involved in the user's system and on any technical modifications carried out which deviate from the standard configuration or the as delivered condition.

If individual designs have been created for specific customers on the basis of series models, other technical performance data may apply.

Before operation begins, the relevant operating instructions and/or assembly or installation instructions should be read and the safety information contained in these instructions should be noted.

KNF reserves the right to make changes to the product and the associated documentation without prior notice to the customer



www.knf.com